

Plum Plug & Heat

Eyewash Box (without refills)

Technical data:

- Dust-proof wall station in impact-proof polystyrene
- Power consumption: 20W
- Power supply: Connect to a 12V DC cigarette lighter or a local converter. The LED will light when the power is connected.
- Heating foil is CE-approved in conformity with low voltage directive 2006/95/EC (EN 60950-1/A2:2013)
- The box should be placed sheltered from the influences of the weather (rain, snow, sun, etc.)
- The box is preset to ensure an eyewash temperature of 16°C to 38°C within an external temperature range of -20°C to +20°C




Electric connection:

- If a transformer is used, it must meet the applicable local requirements for insulation and overcurrent protection
- Plum A/S cannot be held liable for improper choice of transformer resulting in electric shock or other hazards created hereby

Warning:


- If the thermostat is detached from the heating foil, the whole box must be replaced. Otherwise, the content of the bottles is at risk of overheating
- We recommend checking the box temperature minimum 4 times a year. This can be done by simply feeling if the bottles are lukewarm (~ 20°C)



Plum Plug & Heat Eyewash Box, Small

Suitable for 2 bottles of 200 ml or 500 ml Plum Eyewash or pH Neutral with either single or DUO eyecup. Contains no refill.

Art.no.: 4672
Dimensions:
h:270 x w:225 x d:110 mm



Plum Plug & Heat DUO Eyewash Box, Large

Suitable for 2 bottles of 500 ml or 1000 ml Plum Eyewash or pH Neutral with either single or DUO eyecup. Contains no refill.

Art.no.: 4551
Dimensions:
h:357 x w:252 x d:116 mm